



PET PORTABLE LOOP AMPLIFIER

The Easy T PET Portable loop has been designed to cover all aspects of loop operation in places where a fixed wired loop is not practicable.


- Stand alone unit with internal microphone
- Two external microphone sockets
- Vertical operation for counters
- Flat operation for Lecture & Meeting Rooms
- External loop socket (up to 20m² loop)
- Fully automatic operation
- PSU & charger included
- Compliant with IEC118-4 (BSEN60118-4)



The case has been specially designed to operate in a near vertical position for use on counters or on desks in a one to one situation, or to lie flat so it can be used in a teaching or meeting environment without line of sight obstruction.

For larger meetings the PET can cover up to 20m² using the PETEX external loop cable kit and either the internal microphone or up to two external microphones (ETCLM tie-clip type or PETBM boundary microphone).

PETEX external loop cable kit



PETBM boundary microphone



All the audio processing circuitry is fully automatic, and uses a dynamic processor to alter the microphone gain helping to correct for poor microphone technique, and a dynamic noise control to eliminate hiss. A battery low light is provided on the rear and the unit can be operated whilst charging. The high capacity battery allows for up to 8 hours operation from a single charge. The unit can be carried in the optional PETCS soft carry case along with the PSU and any microphones.